

Rittal – The System.

Faster – better – everywhere.



CP 6148.000 Twin castors

State: 14/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6148.000 - Twin castors

For mobile use, for mounting directly on the enclosure.

Features

| | |
|---|---|
| Model No. | CP 6148.000 |
| Product description | For mobile use, for mounting directly on the enclosure. |
| Colour | Black with grey running surface |
| Supply includes | 4 twin castors, 2 x with, 2 x without locks Assembly parts |
| To fit | Enclosure type: VX Enclosure type: VX IT Enclosure type: TS Enclosure type: TS IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller |
| Clearance floor | 85 mm |
| Max. load capacity (static) per component | 750 N |
| To fit Model No. | 6106.200 6106.300 |
| Dimensions | Thread: M12 x 20 |
| Packs of | 1 pc(s). |
| Net weight | 1,115 kg |
| Gross weight | 1,293 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC002621 |
| ECLASS 8.0 | 27189262 |

Features

Product description

CP Twin castors, 2 each with/without lock, static load per castor 75 kg