

**Rittal – The System.**

Faster – better – everywhere.



**DK 7030.095**

**CMC III CAN bus connection cable**

State: 14/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7030.095 - CMC III CAN bus connection cable

Connects CAN bus units for information and power transmission.

## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | DK 7030.095  |
| Product description               | For connecting the PU to the CAN bus sensors III, units III and control units III as a bus, also for cabling together. Because it is available in different lengths, the CMC III system can be adapted to various applications and built to a custom design. |
| Applications                      | For connecting the CAN bus units.<br>Information and power transfer of the individual CAN bus units.   |
| Length                            | 10 m   |
| Dimensions                        | Length: 10 m   |
| Interfaces/connections            | Connector (type): RJ45RJ45   |
| Operating temperature range       | 0 °C...55 °C   |
| Ambient humidity (non-condensing) | 5...95 %   |
| Packs of                          | 1 pc(s).   |
| Net weight                        | 0,37 kg  |
| Gross weight                      | 0,42 kg  |
| Customs tariff number             | 85444290   |
| ETIM 9                            | EC000313   |
| ECLASS 8.0                        | 27189253   |
| Product description               | DK CMC III CAN bus connection cable, L: 10 m, type: RJ45   |

# Tender text

7030.095

CMC III CAN bus connection cable

Packs of 1

This can be used to connect the PU with the CAN bus sensors, units and control units as a bus. Also for cabling together. The cable is used to transmit information and power to the individual CAN bus units.

Technical specifications:

Connector 1: RJ45

Connector 2: RJ45

Length: 10 m

Temperature application range:

0 °C to 55 °C

Humidity range:

5% to 95% relative humidity, non-condensing

Included in the pack: Cable and cable holder