

# Rittal – The System.

Faster – better – everywhere.



## DK 7827.221

## Mounting angles, 482.6 mm (19")

State: 13/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7827.221 - Mounting angles, 482.6 mm (19") for TS

L-shaped mounting angles, also for accommodating server system installation kits.

## Features

Model No.	DK 7827.221
Design	L-shaped mounting angle
Benefits	Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level. L-shaped mounting angles accommodate the installation kits of server systems Suitable for 482.6 mm (19") partial installation
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of the 482.6 mm (19") installed equipment.
Material	Sheet steel, 2 mm
Supply includes	Assembly parts
Units	47 U
Note	Please select slide rails according to the relevant 482.6 mm (19") distance between levels. If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used.
To fit	Enclosure type: TS Height: 2,200 mm
Packs of	2 pc(s).
Net weight	4,958 kg
Gross weight	5,218 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

# Features

---

Product description

DK-TS Mounting angles, 482.6 mm (19"), L-shaped mounting angle,  
For H: 2200 mm, 47 U

## Tender text

DK-TS mounting angles, L-shaped, 47 U

Technical specifications: 2 mm sheet steel, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated