

**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.315**

**RiLineX NH fuse-switch  
disconnecter**

State: 13/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.315 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



## Features

|   |   |
|---|---|
| Model No.                                     | RX 9362.315   |
| Design  | For 60 mm busbar systems  |
| Benefits                                      | Cover: can be locked and prepared for a lead seal<br>Voltage test through separate opening<br>Tool-free changeover of the cable outlet<br>Park position for simpler maintenance work<br>High rated voltage 800 V ready<br>All variants also available with electronic fuse monitoring |
| Material                                      | Polyamide (PA 6)<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated  |
| Colour  | RAL 9005<br>RAL 35745   |
| Supply includes                               | Connectors for electronic fuse monitoring   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Cable outlet                                  | Top/bottom  |
| Type of electrical connection                 | Screw M10   |
| Fuse inserts                                  | NH 3  |

# Features

|                                      |   |
|--------------------------------------|---|
| Rated operating voltage              | 690 V AC  |
| For NH size                          | 3   |
| Test specification                   | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts) |
| Dimensions                           | Width: 250 mm<br>Height: 348.6 mm<br>Depth: 134.9 mm  |
| Operating temperature range          | -5 °C...35 °C   |
| Storage temperature range            | -25 °C...70 °C  |
| To fit busbars                       | 15 x 5/10<br>20 x 5/10<br>30 x 5/10                   |
| To fit busbar system                 | RiLineX<br>RiLine60                                   |
| Number of poles                      | 3-pole  |
| Contamination level                  | 3   |
| with electronic fuse monitoring      | Yes   |
| IP protection category to IEC 60 529 | IP 2XB  |
| Fire load                            | 47,58 MJ/m <sup>2</sup>                               |
| Heat loss max.                       | 101 W   |
| Packs of                             | 1 pc(s).  |
| Net weight                           | 4,7 kg  |
| Gross weight                         | 4,83 kg   |
| Copper weight (kg per piece)         | 2,255   |
| Customs tariff number                | 85369095  |
| ETIM 9                               | EC001040  |

# Features

---

## Product description

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

# Approvals

---

## Approvals

CQC-CCC

## Explanations

Declaration of conformity  
PCF-declaration

# Tender text

RiLineX NH fuse-switch disconnecter (size 3 mit ESÜ)

NH fuse-switch disconnecter for  
60 mm busbar systems.

The device can be adjusted to rail thickness without tools.

Other properties include sealability,

Voltage test via separate openings,

Parking position for the cover and lockability with  
padlocks in the open position (service case).

Rated voltage 690 V AC.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm

Busbar dimensions: 5/10 mm

Rated current: 630 A

Type of electrical connection: Screw M10

Cable outlet: top/bottom

Dimensions: 250 mm x 348 mm x 134 mm (BxHxT)

Feature: Electronic fuse monitoring  
Manufacturer: Rittal GmbH & Co. KG  
Type: 9362315