

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.233 Digital input module

State: 15/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.233 - Digital input module REM 800-DI 14

The digital input module extends the functional scope of the REM 801 network analyser by a further 14 digital inputs.

## Features

|  |                           |
|--|---------------------------|
| Model No.  | SV 9393.233               |
| Operating temperature range  | -10 °C...55 °C            |
| Storage temperature range  | -25 °C...70 °C            |
| Ambient humidity (non-condensing)                                  | 5...25 %                  |
| Contamination level  | 2                         |
| Counter frequency max.   | 20 Hz                     |
| Input signal low   | 0...5 V DC                |
| Input signal high  | 18...28 V DC              |
| IP protection category to IEC 60529                                | IP 20                     |
| For mounting on support rails                                      | Yes                       |
| Connection of round conductors, fine wire without wire end ferrule | 0.2 - 1.5 mm <sup>2</sup> |
| Connection of round conductors, single-wire                        | 0.2 - 1.5 mm <sup>2</sup> |
| Connection of round conductors, multi-wire                         | 0.2 - 1.5 mm <sup>2</sup> |
| Connection for round conductor                                     | AWG 16 - 24               |
| Packs of   | 1 pc(s).                  |
| Net weight   | 0,29 kg                   |
| Gross weight   | 0,295 kg                  |
| Customs tariff number  | 85389099                  |

# Features

---

Product description

SV Digital input module REM 800-DI 14

# Approvals

---

Explanations

Declaration of conformity