

# Rittal – The System.

Faster – better – everywhere.



## DK 7979.335 PDU switched

State: 18/04/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7979.335 - PDU switched

High-end IT rack power distribution: Smart PDU with measurement function per phase and individually switchable output slots.



## Features

---

Model No.	DK 7979.335
Product description	High-end power distribution in a compact design for IT network and server racks. With switching function and power measurement at the infeed or per phase.
Benefits	<p>For vertical mounting, it may be attached in the zero-U space of the Rittal VX IT or TS IT rack with no need for tools</p> <p>Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white)</p> <p>Tool-free divider kit for VX IT</p> <p>PDU self-supplied, no external power supply required</p> <p>Measurement accuracy <math>\pm 1\%</math> (kWh) to EN 62 053-21</p> <p>Programmable startup behaviour following voltage recovery (on/off/last status)</p> <p>Programmable switching behaviour (time/programmable logic)</p> <p>Integral real-time clock with battery buffering (max. 10 years, battery replaceable)</p> <p>Integral electromagnetic buzzer for acoustic alarms</p> <p>Adjustable limit values (warning/alarm) for voltage, current, output</p> <p>Operating hours meter, total and cyclical, resettable</p>

---

# Features

---

## Technical specifications

Display/controller unit in the PDU enclosure rotatable through 180° and replaceable  
Integral, fully-redundant power pack, power supply from all phases  
Error-tolerant PDU power supply redundant across all phases  
Voltage V, current A, frequency Hz  
Active power, active energy, apparent power, apparent energy  
Power factor (cosPhi) and phase angle  
Zero conductor current measurement/load imbalance detection  
Fuse monitoring for PDUs with integral fuse  
Monitoring of the optionally available overvoltage protection  
Bright TFT display, 128 x 128 pixels (RGB) with back-lighting and energy-saving mode to display output data and basic PDU configuration  
Position sensors for display rotation and correct PDU representation on the website  
Multi-colour LEDs (green/amber/red) to indicate switching states and warning/alarm limits per phase or infeed  
Power LED to indicate voltage  
Power-saving design, minimal intrinsic power consumption

---

## Material

Aluminium section, black anodised  
Slots: Plastic

---

## Supply includes

Assembly parts

---

## Options

Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure  
Residual current measurement (type B) per infeed/phase/fuse  
Monitoring of the optionally available overvoltage protection  
CMC III CAN bus sensors may be connected for ambient monitoring, max. 16 sensors  
Other enclosure colours are available  
Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure  
Residual current measurement (type B) per infeed/phase/fuse  
Monitoring of the optionally available overvoltage protection  
CMC III CAN bus sensors may be connected for ambient monitoring, max. 16 sensors  
Other enclosure colours are available

---

# Features

---

Measurement functions, description	Emergency power supply to PDU web server via PoE, sequential disconnection of the outputs Switching function per output slot Avoids overload peaks: Sequential activation of the outputs following voltage recovery Relay states are saved even in the event of a power failure Bistable relays: Low current consumption and high switching capacity, also suitable for higher starting currents up to max. 300 A Grouping: Joint switching of multiple outputs Measurement per phase or infeed Powerful CPU (ARM Cortex A8) Digital input (floating contact) Additional alarm output/relay output (changeover contact)
Dimensions	Width: 44 mm Depth: 70 mm Length: 1,095 mm
No. of sockets and type	18 x C13 / 3 x C19
Sockets	18 x C 13 3 x C 19
Rated operating voltage	400 V (AC)
Rated current (max.)	16 A
Power consumption	11 kW
Infeeds	Phases per infeed: 3~
Length of connection cable	3 m
Type of electrical connection	CEE
Interfaces	USB 2.0 port (USB-A) for mass configuration, firmware updates & data logging CAN bus interface (RJ 45) for a maximum of 16 ambient sensors Serial interface RS232 (RJ12) for LTE unit, scripting, CLI Use of own certificates/TLS 1.2 E-mail forwarding in case of alarm (SMTP) User administration including rights management LDAP(S)/Radius/Active Directory connection Syslog server connection (max. 2 servers) Fully redundant Ethernet interface 10/100/1000 Mbit/s

---

# Features

Directives	EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU
Standards	EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21
Protocols	Web server (HTTP, HTTPS, SSL) SSH, Telnet, NTP TCP/IP v4 & v6, DHCP, DNS SNMP v1, v2c & v3, Modbus/TCP, OPC-UA MIB for linking into 3rd party DCIM software FTP/SFTP (update/file transfer)
Operating temperature range	5 °C...50 °C
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-20 °C...70 °C
To fit	Enclosure type: VX IT enclosure frame: ≥ 1,200 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm
Packs of	1 pc(s).
Net weight	4,001 kg
Gross weight	4,5 kg
Customs tariff number	85366990
ETIM 9	EC002762
ETIM 8	EC002762
ECLASS 8.0	27142604
Product description	DK PDU international, switched, compact basic power distribution incl. energy measurement per phase, individually switchable output slots, with network interface and display, WLD: 44x1095x70 mm, IEC 60 320: 18x C13 + 3x C19

# Approvals

---

Approvals

TÜV

---

Explanations

Declaration of conformity

# Tender text

Compact power distributor for deployment in IT server and network enclosures. Vertical installation in the Zero-U space using the supplied universal brackets for common IT racks. Suitable for tool-free quick assembly in the Rittal VX IT and TS IT racks using the special supplied plug-%-play fastener. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed with slot covers available as accessories. This precludes an unintentional overloading of individual phases and circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A fixed-mounted connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment.

The PDU switched has extensive measurement functions for the current and power monitoring of each phase. And switching functions for each output slot. The integral TFT colour display enables the basic configuration setting and quick access of the electrical consumption data. Two Gigabit network interfaces and the integrated Web server allow access and data transmission using various protocols. The consumption parameters can be forwarded to a DCIM software via SNMP, OPC-UA, Modbus/TCP. For monitoring the ambient parameters, up to 16 sensors (for example temperature / humidity / smoke / leakage / access) as well as VX IT and TS IT handle systems from the CMC accessories program can be connected to the CAN sensor interface.

Optionally, an overvoltage protection module (type3) can be placed on the PDU at the infeed; the overvoltage protection module is equipped with arrestors that can be replaced during operation. For intelligent PDUs, the status is monitored via the network interface, the PDU

basic has a floating alarm contact for monitoring the overvoltage protection. As option, intelligent PDU variants can be supplied with an AC/DC sensitive residual current measurement (RCM type B) with up to 6 measurement points. This changes the PDU length and the number of installed slots for each standard length.

Technical specifications switched

Input voltage range (L1-L2-L3/N/PE): 400 VAC, 50-60Hz

input current: 16A

No. of phases: 3

Marking of phases (3-phase PDUs only: L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type IEC 60320/C13 (total): 18

Number of slots type IEC 60320/C13

(per phase/fuse): 6

Number of slots type IEC 60320/C19 (total): 3

Number of slots type IEC 60320/C19

(per phase/fuse): 1

Number of slots type CEE 7/3 (total): -

Number of slots type CEE 7/3

(per phase/fuse): -

No. of circuit breakers: -

Hydraulic-magnetic protective circuit-breaker: 16 A

Slots individually switchable: Yes

Connector PDU input:

EN 60309 / CEE (3L+N+PE, 6h)

Length of connection cable: 3m

Connection cable type: H05-VV

No. of wires: 5

Cable cross-section: 2,5 mm<sup>2</sup>

PDU housing width: 44mm

PDU housing depth: 70mm

PDU housing height: 1095mm

PDU material: Aluminium, anodised, in RAL 9005 (black)<(,<)>

other colours available on request

PDU mounting adaptor (VX IT / TS IT) –Mounting options:

Frame + Zero-U space + cable route

Measurement functions: Measurement per phase or infeed

Values recorded (per phase): Voltage (V), current (A)<(,<)>

frequency (Hz), Active power (kW), active energy (kWh)

apparent power (kVA), power factor

THD (voltage and current) for 3 phases<(,<)>

Crest factor for single-phase  
Neutral conductor current measurement  
fuse monitoring (at 32 A)  
Optional: Residual current monitoring (RCM)  
AC + DC (RCM Typ B)  
max. 6 measurement points per PDU possible  
(input / per phase / per fuse)  
0 mA – 100 mA je RCM  
Voltage measuring range: 90V - 255V  
Voltage resolution 0.1V  
Current measuring range 0 - 16A/32A  
Current resolution 0.1A  
Measuring accuracy typ.  $\pm 1\%$  according to IEC/EN 62 053-21  
Freely adjustable limit values (warning/alarm) for  
for voltage, current, power: Yes  
Controllerboard: can be rotated  
and replaced during operation  
Display: TFT, RGB 128x128 pixels  
Network interface: 2x RJ45, per 10/100/1000 MBit/s  
Supported protocols:  
IPv4 / IPv6, integral web server  
HTTP, HTTPS, SSL, SSH, NTP, Telnet  
TCP/IP v4 and v6, DHCP, DNS, NTP, Syslog  
SNMP v1, v2c und v3, Traps(>,<)>  
FTP/SFTP (update/file transfer)  
OPC-UA, Modbus/TCP(>,<)>  
FTP/SFTP (update/file transfer)<(>,<)>  
E-mail forwarding (SMTP)  
User administration including rights management: Yes  
LDAP(S)/Radius/Active Directory connection: Yes  
USB port for firmware update+data logging functions: Yes  
Initial commissioning / mass configuration:  
yes, with predefined CSV file  
CAN bus interface: RJ45<(>,<)>  
for connecting 16 sensors  
CAN sensor types: Temperature<(>,<)>  
temperature/humidity (combined), infrared access sensor  
leakage, ariflow, EFD, NH measurement module, smoke alarm  
vandalism, differential pressure<(>,<)>  
VX IT / TS IT handle system  
Plug & play drivers - Rittal RiZone DCIM software: Yes  
Digital input: 1

Alarm relay: 48 V DC/2 A  
Serial interface: RS232 (e.g. for LTE unit 7030.571)  
Conformity: CE  
Standards:  
Safety: EN 62368  
EMV:  
EN 55022 / B  
EN 61000-4-2  
EN 61000-4-3  
EN 61000-6-2  
EN 61000-6-3  
Safety Directive: 2014/35/EU  
EMC Directive: 2014/30/EU  
MTBF (at 40°C) 100.000 hours  
Protection category: IP20 (EN 60529)  
Protection class: Class 1  
Pollution degree: 2  
Overvoltage category: II  
Environmental properties: 2011/65/EU (RoHS 2), WEEE  
Storage temperature: -20°C to +70°C  
Ambient temperature: +5°C to +50°C  
Ambient humidity: 10-95% rel. humidity, non-condensing  
Connector lock for C14 and C20 connectors: 1x  
(further connector locks optional - DK 7979.020)  
Covers C13 (optional accessory): DK 7955.010  
Covers C19 (optional accessory): DK 7955.015  
Type: Rittal PDU switched Model No.: DK 7979.335