

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.562 Current transformer

State: 08/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.562 - Current transformer

## Features

Model No.	SV 9393.562
Design	Output voltage 333 mV
Material	Polyamide Fire protection corresponding to UL 94
Colour	RAL 9005
Supply includes	2 plug-in feet 2 insulating caps 1 primary bar clamp 2 grub screws
To fit busbars	60 x 40
Primary current	800 A
Standards	EN 61869-1/ 2 EN 42600 VDE 0100 EN 50274 / VDE 0660-514 DGUV regulation 3
Dimensions	Width: 96 mm Height: 121 mm Depth: 30 mm
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Fundamental frequency	50...60 Hz
Accuracy Class	0,5
Insulation material (class)	F
Packs of	1 pc(s).

# Features

---

Net weight	0,295 kg
Gross weight	0,301 kg
Customs tariff number	85043129
ETIM 9	EC002048
Product description	SV Current transformer 800 A, 61 mm

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------