


# Rittal – The System.

Faster – better – everywhere.



## VX 8618.822 EMC gland plate

State: 02/07/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8618.822 - EMC gland plate for VX

For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | VX 8618.822  |
| Product description   | For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates. |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Supply includes       | 1 gland plate with T-head punching<br>1 sliding gland plate<br>2 EMC seals   |
| Note on Model No.     | For one enclosure half only  |
| To fit                | Enclosure type: VX<br>Width: = 1,000 mm  |
| Note                  | Standard-compliant IP protection category not supported  |
| Packs of              | 1 pc(s).   |
| Net weight            | 1,5 kg   |
| Gross weight          | 1,78 kg  |
| Customs tariff number | 94039910   |
| ETIM 9                | EC002620   |
| ECLASS 8.0            | 27189261   |
| Product description   | VX EMC gland plate, width 1000 mm  |