

Rittal – The System.

Faster – better – everywhere.



VX 8619.460 Cable clamp rail

State: 06/03/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.460 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.460
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX SE installation options	In enclosure width 1800 mm, in the base
VX base/plinth installation options	In base/plinth width 1800 mm, in conjunction with holder/spacer
To fit	Base/plinth system VX
Dimensions	Length: 1,754 mm
To fit	Enclosure type: VX SE Width: = 1,800 mm
Suitable for width	1.800 mm
Packs of	2 pc(s).
Net weight	7,7 kg
Gross weight	9,38 kg
Customs tariff number	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	VX Cable clamp rail, mounting angle, for W: 1800 mm