

Rittal – The System.

Faster – better – everywhere.



KX 1576.000

E-box KX, stålplåt

State: 2025-05-10 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1576.000 - E-box KX, stålplåt

Kopplingslådan KX, E-Box KX, i stålplåt ger hög montagekomfort samt flexibilitet vid val av låssystem.



Features

Art. nr.	KX 1576.000
Produktbeskrivning	Kopplingslådan KX, E-Box KX, i stålplåt ger hög montagekomfort samt flexibilitet vid val av låssystem.
Material	Skåp: Stålplåt Dörr: Stålplåt, omgivande inskummad PU-tätning
Ytbehandling	Skåp och dörr: Doppgrunderade, pulverlackerade på utsidan, strukturlack Montageplåt: förzinkad
Färg	RAL 7035
Leveransens omfattning	Skåp med dörr Montageplåt Vridlås med 3 mm låsinsats 180°-gångjärn
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Kapslingsklass IP enligt EN 60 529	IP 66

Features

Typklassning motsvarande UL 50E	Typ 1 Type 3R Type 4 Typ 12
IK-kod	IK08
Dimension	Bredd: 380 mm Höjd: 300 mm Djup: 155 mm
Mått för montageplåt (B × H)	365 mm x 275 mm
Materialtjocklek låda	1,25 mm
Materialtjocklek dörr	1,25 mm
Materialtjocklek montageplåt	2 mm
Lås	Antal lås: 1
Grundmaterial	Stålplåt
Förpackningsenhet	1 st.
Nettovikt	6.6
Bruttovikt	6.635
PCF per pack (cradle-to-gate)	24 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Tullvarukod	94032080
EAN	4028177816626
E-Number Sweden	E3465238
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Certificates

Kapslingsklass

Explanations

Tillverkarens deklARATION
Konformitetsförklaring
Konformitetsförklaring UK
PCF-declaration