

Rittal – The System.

Faster – better – everywhere.



SV 9345.015 Fuse holders

State: 13/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.015 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

Features

Model No.	SV 9345.015
Design	For category J fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection for round conductor	AWG 1 - 18
Type of electrical connection	Box terminal
For fuse type (class)	J
Rated operating current max.	30 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports)
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Dimensions	Width: 108 mm Height: 115 mm
Connection of round conductors	1.5 - 50 mm ²
To fit fuses	Diameter: 21 mm Length: 57 mm
Voltage range for indicator lights	110 - 600 V
Electrical ratings UL (SCCR)	200 kA - 600 V, Fuse Class J max. 30 A, JDDZ/7

Features

Number of poles	3-pole
Round conductor cross-section	1.5 - 50 mm ²
Packs of	2 pc(s).
Net weight	0,84 kg
Gross weight	0,966 kg
Copper weight (kg per piece)	0,072
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuseholder, Class J, 30 A, 600 V, 3-pole, (60 mm)

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
