

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.760

## RiLineX component adaptor

State: 15/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.760 - RiLineX component adaptor

RiLineX component adaptor (65 A, 3-pole, including connection cables) in width 54 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



## Features

|                         |  |
|-------------------------|--|
| Model No.               | RX 9360.760  |
| Design                  | With connection cable  |
| Benefits                | For mounting equipment for top hat rail installation, e.g. motor starter<br>Pre-assembled connection cable<br>Simple clip locking for support rails<br>Optional anti-slip guard<br>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)<br>Simple assembly<br>Coordinated accessories reduce the number of different items required |
| Material                | Polyamide (PA 6)<br>Fire protection corresponding to UL 94   |
| Colour                  | RAL 9005<br>RAL 35745  |
| Connection cables (AWG) | AWG 6  |
| Rated current (max.)    | 65 A   |

# Features

|   |   |
|---|---|
| Rated current of round conductor              | 65 A  |
| Rated current of round conductor (UL)         | 65 A  |
| Electrical ratings UL (SCCR)                  | 100 kA - 600 V, Fuse Class RK5 max. 60 A, JDDZ/7<br>20 kA - 600 V, circuit breaker max. 60 A, DIVQ/7<br>65 kA - 480 V, Combination Motor Controller max. 52 A, NKJH/7 |
| Cable outlet                                  | Bottom  |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Length of connection cable                    | 130 mm  |
| Number of poles                               | 3-pole  |
| To fit busbar system                          | RiLineX<br>RiLine60   |
| Dimensions                                    | Width: 54 mm<br>Height: 239.4 mm<br>Depth: 36.2 mm  |
| Support rails Qty/height                      | 1 / 10 mm   |
| To fit busbars                                | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Rated voltage                                 | 690 V AC<br>600 V AC (UL)<br>600 V DC (UL)  |
| Contamination level                           | 3   |
| Standards                                     | IEC 61 439-1/-2<br>UL 508   |
| Rated impulse withstand voltage Uimp          | 8 kV  |
| Rated insulation voltage Ui                   | 1.000 V   |
| IP protection category to IEC 60 529          | IP 2XB  |
| Maximum operating air humidity                | 90 %  |

# Features

|                                   |  |
|-----------------------------------|--|
| Operating temperature range       | -5 °C...55 °C  |
| Storage temperature range         | -25 °C...75 °C   |
| Ambient humidity (non-condensing) | 10...90 %  |
| Packs of                          | 4 pc(s).   |
| Net weight                        | 1,84 kg  |
| Gross weight                      | 1,883 kg   |
| Copper weight (kg per piece)      | 0,145  |
| Customs tariff number             | 85369095   |
| ETIM 9                            | EC001531   |
| Product description               | RiLineX component adaptor (65 A, 3-pole, including connection cables) in width 54 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment. |

# Approvals

|              |  |
|--------------|--|
| Approvals    | UL + C-UL (listed)                           |
| Explanations | Declaration of conformity<br>PCF-declaration |

# Tender text

## RiLineX component adaptor with mounting rail

Device adapters for mounting protective and switching devices for 60 mm busbar systems.

The device is mounted on a pre-assembled, adjustable mounting rail.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 65 A

Connection: 16 mm<sup>2</sup>

Cable outlet: top

Dimensions: 54 mm x 240 mm x 37 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360760