

# Rittal – The System.

Faster – better – everywhere.



## SG 2374.070

### Incandescent lamps

State: 19/05/2024 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2374.070 - Incandescent lamps for steady light components

With BA 15d base.

## Features

Model No.	SG 2374.070
Product description	With BA 15d base.
Benefits	Simple assembly and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Power consumption (approx.)	5 W
Rated impulse withstand voltage, phase to phase	286 V AC
Rated insulation voltage	2000 V AC
Rated operating voltage	260 V
Packs of	3 pc(s).
Weight/pack	0.024 kg
Customs tariff number	85392192
EAN	4028177219892
ETIM 7.0	EC000232
ECLASS 8.0	27371220