

# Rittal – The System.

Faster – better – everywhere.



## HD 2410.111 Cable gland HD

State: 31/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 2410.111 - Cable gland HD

More compact design and the lock nut is included with the supply.



## Features

Model No.	HD 2410.111
Design	EMC
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C...100 °C

## Features

---

IP protection category to IEC 60529	IP69 / IPX8 (5 bar, 30 min)
Packs of	5 pc(s).
Net weight	0.2 kg
Gross weight	0.206 kg
Customs tariff number	73072980
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	HD Cable gland, stainless steel 1.4305, size: M16x1,5, for cables Ø 5-10 mm, EMC version

## Approvals

---

Approvals	UR + C-UR (recognized) VDE
-----------	-------------------------------