


# Rittal – The System.

Faster – better – everywhere.



## HD 2410.131 Cable gland HD

State: 13/02/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# HD 2410.131 - Cable gland HD

More compact design and the lock nut is included with the supply.



## Features

Model No.	HD 2410.131
Design	EMC
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M25 x 1.5
For cable diameters	12 - 17 mm
Operating temperature range	-20 °C...100 °C

# Features

---

IP protection category to IEC 60 529	IP69 / IPX8 (5 bar, 30 min)
-----------------------------------------	-----------------------------

---

Type rating to UL 50E	Type 1
	Type 2
	Type 4
	Type 4X
	Type 12
	Type 12K
	Type 13

---

Packs of	5 pc(s).
----------	----------

---

Net weight	0.54
------------	------

---

Gross weight	0.581
--------------	-------

---

Customs tariff number	73072980
-----------------------	----------

---

EAN	4028177928664
-----	---------------

---

ETIM 9	EC000441
--------	----------

---

ETIM 8	EC000441
--------	----------

---

ECLASS 8.0	27149109
------------	----------

# Approvals

---

Approvals	UL + C-UL (listed) VDE
-----------	---------------------------