

# Rittal – The System.

Faster – better – everywhere.



## VX 9680.628 Modular enclosure

State: 08/07/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 9680.628 - Modular enclosure Bayed enclosure system VX25

Baying systems VX, for installation with partial doors and internal separation in a modular design.

## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | VX 9680.628  |
| Material                          | Sheet steel, 1.5 mm  |
| Surface finish                    | Enclosure frame: Dipcoat-primed<br>Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint<br>Gland plates: Zinc-plated |
| Colour                            | RAL 7035   |
| Supply includes                   | Enclosure frame<br>Rear panel<br>Gland plates  |
| Protection category to IEC 60 529 | Up to IP 54, depending on the panels   |
| Test specification                | IEC 61 439-1/-2<br>IEC 61 641  |
| Dimensions                        | Width: 600 mm<br>Height: 2,200 mm<br>Depth: 800 mm   |
| Packs of                          | 1 pc(s).   |
| Net weight                        | 47,25 kg   |
| Gross weight                      | 52,2 kg  |
| PCF per pack (cradle-to-gate)     | 137.5 kg CO2 eq (Cat B)  |
| Note on PCF category              | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                           |
| Customs tariff number             | 94032080   |
| ETIM 9                            | EC000261   |

# Features

---

ECLASS 8.0

27180101

---

Product description

VX Modular enclosure, WHdepth 600x2200x800 mm, sheet steel

# Approvals

---

Certificates

Surface finish