

Rittal – The System.

Faster – better – everywhere.



SK 3201.970

Toroidal transformer

State: 04/06/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.970 - Toroidal transformer Primary connection 115 V/400 V

For power supply to wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection.

Features

| | |
|--------------------------------------|---|
| Model No. | SK 3201.970 |
| Product description | For the power supply of wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection. |
| Technical specifications | Output 110 VA Voltage tolerance $\pm 10\%$ Primary connection 3500 mm long Secondary connection 1500 mm long For mounting on a 35 mm support rail EN 50 022 |
| Supply includes | Toroidal transformer Assembly parts |
| Packs of | 1 pc(s). |
| Snap-mounting to support rails TS 35 | Yes |
| To fit Model No. | 3363.X0X 3364.X0X 3214.100 3214.700 3215.100 3215.700 |
| Dimensions | Width: 105 mm Height: 123 mm Depth: 55 mm |
| Rated operating voltage | 115 V (primary), 1~, 50 Hz/60 Hz 230 V (secondary), 1~, 50 Hz/60 Hz |
| Net weight | 2.1 kg |
| Gross weight | 2.355 kg |

Features

| | |
|-----------------------|---|
| Customs tariff number | 85043121 |
| ETIM 9 | EC000855 |
| ETIM 8 | EC000855 |
| ECLASS 8.0 | 27180704 |
| Product description | SK Toroidal transformer, 115 V (primary), 1~, 50/60 Hz, 230 V (secondary), 1~, 50/60 Hz, WHD: 105 x 123 x 55 mm |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|