

Rittal – The System.

Faster – better – everywhere.



CS 9791.035

Outdoor wall-mounted enclosures

State: 03/07/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9791.035 - Outdoor wall-mounted enclosures

Outdoor enclosures for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out at the bottom and integrated louvres on the rear panel and side panels for ventilation.



Features

| | |
|---------------------|---|
| Model No. | CS 9791.035 |
| Product description | Outdoor enclosures for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out in the bottom and integrated louvres on the rear panel and side panels for ventilation. |
| Material | Enclosure and mounting plate: Aluminium, AlMg3 Door, inner enclosure: Stainless steel 1.4301 (AISI 304) |
| Surface finish | Enclosure: Powder-coated, UV-resistant pure polyester |
| Colour | RAL 7035 |
| Supply includes | Double-walled outdoor enclosure, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygostat Outer enclosure with designer cover and security lock 3524 E 2 C rails on the rear panel |
| Dimensions | Width: 530 mm Height: 700 mm Depth: 265 mm |

Features

| | |
|-------------------------------------|--|
| Clearances | Clearance width: 440 mm Clearance height: 545 mm Clearance depth: 195 mm |
| Dimensions mounting plate (W x H) | 430 mm x 535 mm |
| Inner enclosure | Width: 460 mm Height: 565 mm Depth: 220 mm |
| Lock | Lock version: Cam Number of locks: 2 |
| IP protection category to IEC 60529 | IP 55 |
| Note | Extended delivery times. |
| Basic material | Aluminium |
| Packs of | 1 pc(s). |
| Net weight | 16,625 kg |
| Gross weight | 17,5 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | CS Wall-mounted enclosure, WHD: 530x700x265 mm, aluminum, with mounting plate, Enclosure-within-an-enclosure concept |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|

Tender text

Outdoor wall-mounted enclosure

Dual-shell outdoor aluminium enclosure for pole or wall mounting, consists of an outdoor enclosure with louver ventilation, security lock and a lockable interior enclosure with mounting plate.

Interior enclosure:

Body: 1.5 mm aluminium, folded and welded from a single piece with protection channel around the door opening.

Screwed on gland plate fitted at top (W x D = 97.5 x 65.5 mm) and bottom (W x D = 182 x 52 mm). Thermostat mounting holder fitted at top left.

Door: 1,5 mm stainless steel, mounted, with foamed-in sealer and screwed on hinges, 180° opening angle, cam lock with security lock

Mounting plate: 2 mm aluminium

Outer enclosure:

Enclosure with removable cover and security lock design. Ventilation louvers in upper left, right and rear sections; rows of ventilation holes in the left and right side of the base. Screwed on gland plate at the bottom. Two C-rails screwed on at the rear for mounting a pole attachment. Enclosure cover with recessed handle.

Material

Interior enclosure, outer enclosure and mounting plate:
Aluminium AlMg3

Surface:

Interior enclosure and outer enclosure: Powder coated in RAL 7035

Mounting plate: zinc-plated, passivated

Dimensions:

Interior enclosure: W x H x D: 460 x 565 x 220 mm

Outer enclosure: W x H x D: 530 x 700 x 265 mm

Protection category:

IP 55 to EN 60 529/10.91

