


Rittal – The System.

Faster – better – everywhere.



VX 8660.053

Base/plinth corner pieces with
base/plinth trim panels, front and
rear for VX base/plinth system,
stainless steel



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDRICH LOH GROUP

VX 8660.053 - Base/plinth corner pieces with base/plinth trim panels, front and rear for VX base/plinth system, stainless steel Nytt utförande

Base/plinth corner pieces with front and rear trim panel. Large openings in the base/plinth corner piece for optimum access to the screw connection. Seamlessly bayable.



Features

Art. nr.	VX 8660.053
Material	Sockelhörndel: Rostfritt stål 1.4301 (AISI 304) Sockelplåt fram/bak: Rostfritt stål 1.4301 (AISI 304) Täckkåpor: ABS
Ytbehandling	Streckslipat, korn 400
Leveransens omfattning	Inkl. fastsättningsmaterial 4 sockelhörndelar 4 täckhylsor 2 sockelplåt fram/bak, 100 mm hög
Observera:	Side base/plinth trim panels are required to finish off a base/plinth unit and also for additional stability between the base/plinths. If necessary, the cover caps included with the supply may be exchanged for stainless steel cover caps for VX base/plinth system, stainless steel. Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Dimension	Höjd: 100 mm

Features

Passar för	Skåptyp: VX VX SE TS PC Bredd: = 1.200 mm
Typklassning motsvarande UL 50E	Typ 1 Type 3R Type 4 Type 4X Typ 12
Förpackningsenhet	2 st.
Nettovikt	6.4
Bruttovikt	6.5
Tullvarukod	94039910
EAN	4028177037892
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------