Rittal - The System.

Faster – better – everywhere.



VX 8660.061

Base/plinth corner pieces with base/plinth trim panels, front and rear for VX base/plinth system, stainless steel

State: 2025-10-22 (Source: rittal.com/se-sv)



ENCLOSURES

POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

© Rittal 2025 2

VX 8660.061 - Base/plinth corner pieces with base/plinth trim panels, front and rear for VX base/plinth system, stainless steel Nytt utförande

Base/plinth corner pieces with front and rear trim panel. Large openings in the base/plinth corner piece for optimum access to the screw connection. Seamlessly bayable.





Features

Art. nr.	VX 8660.061
Material	Sockelhörndel: Rostfritt stål 1.4301 (AISI 304)
	Sockelplåt fram/bak: Rostfritt stål 1.4301 (AlSI 304)
	Täckkåpor: ABS
Ytbehandling	Streckslipat, korn 400
Leveransens omfattning	Inkl. fastsättningsmaterial
	4 sockelhörndelar
	4 täckhylsor
	1 sockelplåt, fram/bak, 200 mm
	2 sockelplåt fram/bak, 100 mm hög
Observera:	Side base/plinth trim panels are required to finish off a base/plinth unit and also for additional stability between the base/plinths. If necessary, the cover caps included with the supply may be exchanged for stainless steel cover caps for VX base/plinth system stainless steel.
	Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Dimension	Höjd: 200 mm

© Rittal 2025

3

Features

Passar för	Skåptyp: VX
	VX SE
	TS
	PC
	Bredd: = 800 mm
Typklassning motsvarande UL 50E	Typ 1
	Type 3R
	Type 4
	Type 4X
	Typ 12
Förpackningsenhet	2 st.
Nettovikt	7.6
Bruttovikt	8.074
Tullvarukod	94039910
EAN	4028177037939
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA