

Rittal – The System.

Faster – better – everywhere.



RX 9362.250

NH-säkringslastfrånskiljare

State: 2025-06-01 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.250 - NH-säkringslastfrånskiljare

RiLineX NH fuse-switch disconnecter in size 2 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 120 to max. 300 mm². Cable outlet can be at the top or bottom, as required.

Features

Art. nr.	RX 9362.250
Fördelar	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work High rated voltage 800 V ready All variants also available with electronic fuse monitoring
Material	Polyamid (PA 6) Brandklassad enligt UL 94 Kontaktbanor: försilvrad elektrolytkoppar
Färg	RAL 9005 RAL 35745
För skensystem med centrumavstånd	60 mm
Kabelutgång	uppe/nedtill
Anslutningstyp (elektrisk)	Tunnelklämma
Märkström max.	400 A
Märkspänning	690 V AC
För NH-storlek	2
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (säkringsinsatser)

Features

Dimension	Bredd: 209 mm Höjd: 299 mm Djup: 135 mm
Driftstemperatur	-5 °C...35 °C
Förvaringstemperatur	-25 °C...70 °C
Passar för samlingsskenor	15 x 5/10 20 x 5/10 30 x 5/10
Passar för samlingsskenesystemet	RiLineX RiLine60
Poltal	3-polig
Nedsmutningsgrad	3
Kapslingsklass IP enligt IEC 60 529	IP 2XB
Anslutning av rundledare, fintrådiga utan ändhylsa	35 - 240 mm ²
Anslutning av rundledare, fintrådig med ändhylsa	35 - 240 mm ²
Förpackningsenhet	1 st.
Nettovikt	6
Bruttovikt	6
Kopparandel (kg/st)	1.75
Tullvarukod	85369095
ETIM 9	EC001040