

Rittal – The System.

Faster – better – everywhere.



SZ 2411.871

Cable gland, brass

State: 15/05/2024 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.871 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.871
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 54 mm
Thread	M63 x 1.5
Thread length	14 mm
Min. cable diameter	34 mm
Max. cable diameter	44 mm
Operating temperature range	-40 °C...100 °C
torque	50 Nm
Width across flats	64 mm
Dimensions	Thread: M63 x 1.5 Thread length: 14 mm
Type rating to UL 50E	Type 4X
Packs of	1 pc(s).
Weight/pack	0.52 kg
Customs tariff number	73269098

Features

EAN	4028177810020
ETIM 7.0	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity