

# Rittal – The System.

Faster – better – everywhere.



## SK 3120.200 Speed control

State: 04/08/2025 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3120.200 - Speed control for filter fans and air/air heat exchangers

Temperature-dependent speed control to minimise noise and save energy in part-load operation.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | SK 3120.200  |
| Product description      | Temperature-dependent speed control to minimise noise and save energy in part-load operation.                              |
| Technical specifications | For mounting on a 35 mm support rail EN 50 022<br>Phase cross-over with microcontroller<br>Maximum fan output 300 W or 2 A |
| Supply includes          | Speed control<br>NTC sensor, length 1.80 m   |
| Packs of                 | 1 pc(s).   |
| Speed                    | 100 %  |
| Note                     | Only suitable for use with single-phase AC motors and equipment<br>Not suitable for EC motors                              |
| Dimensions               | Width: 105 mm<br>Height: 90.5 mm<br>Depth: 60.2 mm   |
| Setting range            | 20 °C...55 °C  |
| Rated operating voltage  | 100 V - 230 V  |
| Net weight               | 0.359  |
| Gross weight             | 0.39   |
| Customs tariff number    | 90321020   |
| EAN                      | 4028177631441  |
| E-Number Sweden          | E7239754   |
| ETIM 9                   | EC000256   |
| ETIM 8                   | EC000256   |

# Features

|            |          |
|------------|----------|
| ECLASS 8.0 | 27142320 |
|------------|----------|

# Approvals

|              |   |
|--------------|---|
| Approvals    | UR  |
| Certificates | EAC   |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |