


# Rittal – The System.

Faster – better – everywhere.



## SV 3528.000

## PLS special busbars E-Cu

State: 14/07/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3528.000 - PLS special busbars E-Cu

Lengths range from 495 mm to 2400 mm.



## Features

|                              |  |
|------------------------------|--|
| Model No.                    | SV 3528.000                                |
| Material                     | E-Cu                                       |
| Bar thickness                | 10 mm                                      |
| Cross-section                | 900 mm <sup>2</sup>                        |
| Note                         | May be cut individually to required length |
| Busbar type                  | Busbar E-Cu                                |
| To fit busbar system         | PLS 1600                                   |
| Dimensions                   | Length: 695 mm                             |
| To fit                       | Width: = 800 mm                            |
| Packs of                     | 3 pc(s).                                   |
| Net weight                   | 16.86                                      |
| Gross weight                 | 16.86                                      |
| Copper weight (kg per piece) | 5.62                                       |
| Customs tariff number        | 74071000                                   |

# Features

|            |               |
|------------|---------------|
| EAN        | 4028177043787 |
| ETIM 9     | EC001522      |
| ETIM 8     | EC001522      |
| ECLASS 8.0 | 27370303      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

PLS special busbar E-Cu 1600 A  
Bar thickness: 10 mm  
Rated current: 1600 A  
Cross-section: 900 mm<sup>2</sup>  
Length: 695 mm  
Enclosure width: 800 mm  
(Rittal PS/TS/ES enclosure systems)