

Rittal – The System.

Faster – better – everywhere.



AS 4050.318 Thread tapping option

State: 04/07/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.318 - Thread tapping option for Perforex LC 3030

Thread tapping option for Perforex laser centre LC including thread tappers and clamping jaws for M3 – M10.



Features

| | |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | AS 4050.318 |
| Design | Movable tool magazine with 6 magazine slots Tool holder Additional drive unit |
| Product description | Thread tapping option for cutting threaded holes with the Perforex laser centre LC. |
| Benefits | Machining of projects with tapped holes supported Fast, automatic changeover from laser function to thread-tapping function by accommodating an additional machine head |
| Supply includes | Thread tapper Clamping units for M3 – M10 |
| Machinable height (max.) | 600 mm |
| Material thickness | 5 mm |
| To fit Model No. | 4050330 |
| Packs of | 1 pc(s). |
| Net weight | 78 kg |
| Gross weight | 78 kg |
| Customs tariff number | 84669360 |
| ECLASS 8.0 | 36600890 |

Features

Product description

AS Tapping unit LC 3015/3030, Tapping option for Perforex Lasercenter LC, - Including equipped Tool holders M3 - M10., - Tool magazine with 6 slots., - SK30 Tool holder.