

# Rittal – The System.

Faster – better – everywhere.



## SK 3328.500

# TopTherm wall-mounted cooling unit Blue e

State: 04/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3328.500 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".

## Features

Model No.	SK 3328.500
Design	wall-mounted
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Sheet steel
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts Integral electric condensate evaporation
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.1 kW Cooling output L35 L35/60 Hz: 2.39 kW Cooling output L35 L50/50 Hz: 1.52 kW Cooling output L35 L50/60 Hz: 1.76 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 5.8 A At 60 Hz: 6.8 A
Start-up current max.	At 50 Hz: 20 A At 60 Hz: 22 A
Air throughput (unimpeded air flow)	External circuit: 980 m <sup>3</sup> /h Internal circuit: 980 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.44 Refrigeration factor L35 L35 (EER) 60 Hz: 2.21

# Features

Design	wall-mounted
Dimensions	Width: 400 mm Height: 1,580 mm Depth: 295 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.95 kg Global Warming Potential (GWP): 631 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.6 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.86 kW Power consumption L35 L35/60 Hz: 1.08 kW Power consumption L35 L50/50 Hz: 1.02 kW Power consumption L35 L50/60 Hz: 1.23 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Miniature circuit-breaker/fuse: 16 A
Packs of	1 pc(s).
Net weight	67.45 kg
Gross weight	71 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, 2.2 kW, 230 V, 1~, 50/60 Hz, Sheet steel, WHD: 400 x 1580 x 295 mm

# Approvals

---

## Approvals

30 - KC Korea  
UL + C-UL (listed)  
UL + C-UL - FTTA  
UR + C-UR (recognized)

---

## Explanations

FCC  
Declaration of conformity  
Declaration of conformity - F-gas regulation  
Declaration of conformity UK