

Rittal – The System.

Faster – better – everywhere.



SK 3329.104

Wall-mounted cooling units

State: 20/07/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3329.104 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.

Features

Model No.	SK 3329.104
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Design	wall-mounted
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0 kg
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Packs of	1 pc(s).
Net weight	68.4
Gross weight	72
EAN	4028177389434
ECLASS 8.0	27180704

Approvals

Approvals	UL + C-UL (listed) UR + C-UR (recognized)
-----------	--

Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Wall-mounted cooling unit Rittal TopTherm PLUS -
NEMA 4 x, with RiNano coating and
integral condensate evaporation
Useful cooling output to DIN 3168 L35 L35 2500/2750 W
Rated operating voltage 230 V, 1~, 50/60 Hz
Power consumption Pel to DIN 3168 L35 L35 1450/1675 W
Dimensions W x H x D [mm] 405 x 1650 x 368
Refrigerant R 134 a
Temperature range 20°C to 55°C (Setting range +30°C to +55°C)
Temperature control and monitoring via
basic controller with floating fault signal contact
and connection for door-operated switch
Factory setting 35°C
Connection via pluggable terminal strip
Protection category NEMA 4X
Weight 83 kg
Colour RAL 7035