## Rittal – The System.

Faster – better – everywhere.







# AS 4055.212 Hole punch, round

State: 17/11/2025 (Source: rittal.com/sg-en)



# AS 4055.212 - Hole punch, round for sheet steel

For punching round cut-outs

#### **Features**

Model No.	AS 4055.212
Design	With 3 cutting points
Supply includes	Female dies Male dies Tension screw without ball bearing
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	12.7 mm
For threads	M12
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packs of	1 pc(s).
Net weight	0.065
Gross weight	0.08
Customs tariff number	82073010
EAN	4028177808188
ETIM 9	EC000156
ETIM 8	EC000156

© Rittal 2025

### Features

ECLASS 8.0

21049047

© Rittal 2025 3