


Rittal – The System.

Faster – better – everywhere.



SZ 4138.180 Standard light

State: 21/08/2025 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4138.180 - Standard light

Supply voltage: 120 V AC 60 Hz, 230 V AC 50 Hz

Features

| | |
|---|---|
| Model No. | SZ 4138.180 |
| Design | without door operated switch |
| Supply includes | Standard light Light Assembly parts |
| Power consumption | 18 W |
| Ballast | Magnetic ballast |
| Connection options | Door-operated switch Power supply via connectors Through-wiring (creating rows of lights) |
| Light | Fluorescent lamp, base G13 |
| Protection class | I (PE conductor) |
| Switch (type) | Integral on/off/door-operated switch |
| Light – installation type | Screw-fastening |
| Rated impulse withstand voltage, phase to earth | 1500 V AC |
| Rated impulse withstand voltage, phase to phase | 500 V AC |
| Rated insulation voltage | 500 V DC/1s |
| Installation options | TS horizontal section of the roof frame: direct TS, SE vertical section: with TS adaptor bracket SE sections at the front and rear of the roof frame: with TS adaptor bracket SE extrusions at the side of the roof frame: direct AE, CM, TP: with universal bracket AE: with rail for interior installation |

Features

| | |
|-----------------------------|---|
| Dimensions | Width: 682 mm Height: 117 mm Depth: 50 mm |
| Operating temperature range | -15 °C...45 °C |
| Sockets | D, earthing-pin (type F, CEE 7/4) |
| Storage temperature range | -20 °C...70 °C |
| Rated operating voltage | 230 V, 1~, 50 Hz |
| Socket version | D, earthing-pin (type F, CEE 7/4) |
| Packs of | 1 pc(s). |
| Net weight | 1.74 |
| Gross weight | 1.94 |
| Customs tariff number | 94054990 |
| EAN | 4028177092273 |
| ECLASS 8.0 | 27189241 |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|