

Rittal – The System.

Faster – better – everywhere.



VX 5301.336

Gland plate set, multi-piece, solid

State: 09/07/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.336 - Gland plate set, multi-piece, solid for VX IT

Multi-piece gland plate set consisting of solid base plate modules and a sliding panel for cable entry.

Features

| | |
|-------------------------------|--|
| Model No. | VX 5301.336 |
| Product description | Multi-piece gland plate set consisting of solid base plate modules and a sliding panel for cable entry. The solid gland plate module, depth 237.5 mm, may optionally be exchanged for gland plate module variants for cable entry. |
| Benefits | The sequence of individual modules may be freely selected |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Gland plate set Sealing tape Assembly parts 1 gland plate module, solid, depth: 75 mm 1 gland plate module, solid, depth: 175 mm 2 sliding panels, depth: 115 mm |
| To fit | Enclosure type: VX IT Width: = 800 mm Depth: = 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 4.5 kg |
| Gross weight | 4.84 kg |
| PCF per pack (cradle-to-gate) | 14.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Features

Product description

VX IT gland plate module, multi-piece, solid, for width 800 mm, W x D 800 x 600 mm, sheet steel