

**Rittal – The System.**

Faster – better – everywhere.



# SV 3452.500 Conductor connection clamp

State: 05/04/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3452.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

## Features

|   |  |
|---|--|
| Model No.                                       | SV 3452.500  |
| Product description                             | For connecting round conductors and laminated copper bars.   |
| Material  | Sheet steel  |
| Surface finish                                  | Zinc-plated, passivated  |
| Clamping area for laminated copper bars (W x H) | 10.5 x 11 mm   |
| Note  | Wire end ferrules should be used with fine wire conductors   |
| Connection of round conductors                  | 16 - 50 mm <sup>2</sup>  |
| For bar thickness                               | 5 mm   |
| Packs of  | 15 pc(s).  |
| Net weight                                      | 0.81 kg  |
| Gross weight                                    | 1.004 kg   |
| PCF per pack (cradle-to-gate)                   | 3.9 kg CO2 eq (Cat B)  |
| Note on PCF category                            | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number                           | 85369010   |
| ETIM 9  | EC000001   |
| ETIM 8  | EC000001   |
| ECLASS 8.0                                      | 27141146   |
| Product description                             | SV Conductor connection clamp, 16-50 mm <sup>2</sup> , clamping area WH: 10,5x11 mm, for bar thickness 5 mm    |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---

## Tender text

SV conductor connection clamps  
for E-CU busbars and Rittal PLS.

For bar thickness: 5 mm

Connection of round conductors: 16 - 50 mm<sup>2</sup>

Wire end ferrules should be used with  
fine wire conductors.

Clamping area: for laminated copper bars 10.5 x 11 mm

Tightening torque

Conductor connection clamp: 6 - 8 Nm

Material: sheet steel, zinc plated, passivated