## Rittal – The System.

Faster – better – everywhere.





# SV 3560.000 Plate clamp

State: 16/11/2025 (Source: rittal.com/sg-en)



## SV 3560.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

#### **Features**

Model No.	SV 3560.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	34 x 10 mm
To fit busbars	50 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Net weight	0.999
Gross weight	1.043
PCF per pack (cradle-to-gate)	4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177044357
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

## **Approvals**

© Rittal 2025

### **Approvals**

**Explanations** 

Declaration of conformity
Declaration of conformity UK

#### Tender text

SV plate clamps

for E-CU busbars with 3 - 10 mm thickness.

For bar width: up to 50 mm

Clamping area for laminated copper bars:

34 x 10 mm

Tightening torque: 6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated

© Rittal 2025