

Rittal – The System.

Faster – better – everywhere.



IT 5302.042

482.6 mm (19") cable link, depth-variable

State: 12/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 5302.042 - 482.6 mm (19") cable link, depth-variable

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

Features

| | |
|-------------------------|--|
| Model No. | IT 5302.042 |
| Product description | A user-friendly way of creating integrated cable routing between the front and rear 482.6 mm (19") mounting levels within the enclosure. |
| Benefits | <p>Cable entry at the front via brush strip for thermal partitioning of the cable entry zone</p> <p>Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear</p> <p>Fully depth-variable with versatile, infinitely adjustable extension of the cable link</p> <p>Prevents incorrect airflow by partitioning the transition</p> <p>Open at the top for easy retrofitting, even with cables already inserted</p> <p>Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip</p> |
| Material | Sheet steel Brush strip: Plastic, UL 94-V0 |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | Cable link Brush strip |
| Installation options | For attachment between the front and rear 482.6 mm (19") mounting level |
| Distance between levels | 500 - 750 mm |
| Units | 1 U |
| Load capacity (static) | 150 N |
| To fit | for enclosure-independent mounting |

Features

| | |
|-------------------------------|--|
| Note | Assembly parts should be ordered separately |
| Packs of | 1 pc(s). |
| Net weight | 6.8 kg |
| Gross weight | 7.239 kg |
| PCF per pack (cradle-to-gate) | PCF-Wert 18,78 kg Co ² e |
| Customs tariff number | 73269098 |
| Product description | 19" cable bridge, depth-variable, 500 - 750 mm, RAL 9005 |