


# Rittal – The System.

Faster – better – everywhere.



## CP 6380.410

## Optipanel

State: 01/02/2026 (Source: [ittal.com/sg-en](http://ittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6380.410 - Optipanel

Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Super-slimline design, needs hardly more space than the installed equipment itself.



## Features

Model No.	CP 6380.410
Design	Support arm connection Ø 130 mm
Benefits	Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material	Enclosure: Extruded aluminium section Corner pieces: Die-cast zinc Corner protectors: Plastic
General colour	Natural anodised
Colour	Enclosure: Natural anodised Corner pieces: RAL 7035 Corner protectors: similar to RAL 7024
Supply includes	Enclosure with hinged rear panel Seals Seals and assembly parts for front panels
Installation depth	150 mm

# Features

IP protection category to IEC 60529	IP 65
To fit front panel width	520 mm
To fit front panel height	400 mm
Design	Servicing access from the rear
Note	<p>The support arm connection may be swapped over by rotating the enclosure</p> <p>3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C</p> <p>Hinging of the rear panel on the longest enclosure side</p>
Basic material	Aluminium
Lock	<p>Lock version: Cam</p> <p>Number of locks: 2</p> <p>Lock insert: 3 mm double-bit</p>
Packs of	1 pc(s).
Net weight	9.795
Gross weight	10.311
EAN	4028177663169
ETIM 9	EC002504
ECLASS 8.0	27180505

# Approvals

Approvals	UL + C-UL (listed)
Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>