

# Rittal – The System.

Faster – better – everywhere.



## SM 6446.030 Built-in keyboard 19"/4 U

State: 23/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 6446.030 - Built-in keyboard 19"/4 U with integral touchpad

The integral touchpad means that the installation of an additional, correct protection category mouse is no longer required, and cabling is also reduced.



## Features

Model No.	SM 6446.030
Product description	The integral touchpad eliminates the need for installation of an additional, correct protection category mouse, and cabling is also reduced. The short stroke keys are easily identified by edge embossing, less force is required to operate them, and they have good positive key actuation.
Benefits	The separate number pad enables the parameters to be entered quickly Sealed, wipeable surface finish High level of mechanical and chemical resistance as per DIN 42 115.
Material	Front panel: Aluminium
Supply includes	USB connection cable, length 1.8 m Seal Drilling template Assembly parts for surfaces
Dimensions	Width: 482.6 mm Height: 177 mm Depth: 30 mm
Number keys	2.6 N

# Features

Number keys	0.3 mm
Interfaces	1 x USB
Number keys	105
Layout	German
Resolution capacitive touchpad	40 pixels/mm
Lifetime	3 million switching cycles
Dimensions	Thread: M5 Thread length: 20 mm
Operating temperature range	-40 °C...90 °C
IP protection category to IEC 60529	IP 65 (at the front, sealed)
Packs of	1 pc(s).
Net weight	1.44 kg
Gross weight	1.82 kg
Customs tariff number	84716060
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	SM Built-in keyboard 19"/4 U, WHD: 482,6x177x30 mm, Installation depth: 23 mm, german, With integral touchpad

# Approvals

Explanations

Declaration of conformity