Rittal - The System.

Faster – better – everywhere.





SM 6450.020 TFT monitor

State: 18/11/2025 (Source: rittal.com/sg-en)



SM 6450.020 - TFT monitor

Installation variant for surfaces and command panels.

Features

Model No.	SM 6450.020	
Design	without touchscreen	
Product description	Installation variant for surfaces and command panels.	
Benefits	High-quality industrial design Reduced installation work thanks to integral front frame No additional ventilation required Very small installation depth (45 mm)	
Material	Front frame: Aluminium	
Surface finish	Powder-coated	
Colour	RAL 7035	
Supply includes	Seal Hex nuts (for installation in surfaces) VGA cable Threaded bolt M5, for rear mounting Touch variants additionally with integral connection cable and CD-ROM driver With anti-reflection coated safety glass screen.	
Dimensions	Width: 482.6 mm Height: 354.8 mm	
Interfaces	VGA (D-Sub HD 15-pole) DVI-D	
Operating temperature range	0 °C50 °C	
Storage temperature range	-30 °C85 °C	
Note on Model No.	Other variants as resistive touchscreen with serial or USB interface available on request.	
Display brightness	350 cd/m²	
Contrast ratio	1000 : 1	

© Rittal 2025

Features

Diagonal	17"
Hours of operation	50,000 h
On Screen Display (OSD)	Operating buttons at the rear
Reading angle left/right	85 °
Resolution of display	1280 x 1024 pixels
Power consumption Pel	With DC: 20 W
H-Sync. (min./max.)	31.4 - 80 kHz
V-Sync. (min./max.)	60 - 75 Hz
Number of colours	16.7
Resolution of controller	VGA SVGA XGA SXGA
Packs of	1 pc(s).
Net weight	6.897
Gross weight	7.26
Customs tariff number	85286200
EAN	4028177442429
ETIM 9	EC001428
ECLASS 8.0	19200201

Approvals

Explanations	Declaration of conformity	
--------------	---------------------------	--

© Rittal 2025 3