

**Rittal – The System.**

Faster – better – everywhere.



**DK 7485.035**

# Component shelf for frame attachment

State: 04/06/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7485.035 - Component shelf for frame attachment for enclosure widths 600 mm, 800 mm

For installation in enclosures without 482.6 mm (19") accommodation.

## Features

|                      |   |
|----------------------|---|
| Model No.            | DK 7485.035   |
| Design               | Slotted   |
| Product description  | For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation.  |
| Benefits             | Mounting bolts or mounting rails may be installed on a 25 mm pitch pattern in the enclosure depth.<br>Mounting hole for handles provided.   |
| Applications         | For installation in enclosures without 482.6 mm (19") accommodation   |
| Material             | Sheet steel   |
| Surface finish       | Spray-finished  |
| Colour               | RAL 7035  |
| Supply includes      | Component shelf, slotted<br>2 mounting rails  |
| Installation options | Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange<br>Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange<br>Depth variable: Component shelf, 50 kg with telescopic slides on punched sections without mounting flange |
| Load capacity        | 100 kg area load  |
| Assembly instruction | Additionally, two punched sections with mounting flanges are required for the inner mounting level  |
| Note                 | Max. depth of component shelves = Enclosure depth - 100 mm.   |

# Features

|                               |  |
|-------------------------------|--|
| Dimensions                    | Width: 671 mm<br>Height: 45 mm<br>Depth: 500 mm  |
| To fit                        | Enclosure type: VX<br>VX IT<br>TS IT<br>Width: 800 mm  |
| Packs of                      | 1 pc(s).   |
| Net weight                    | 8.17 kg  |
| Gross weight                  | 8.6 kg   |
| PCF per pack (cradle-to-gate) | 32.8 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 94039910   |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |
| Product description           | DK Component shelf, WHD: 671x45x500 mm, 100 kg, For frame attachment, For W: 800 mm, RAL 7035                  |

# Tender text

Component shelves for 800 mm wide network enclosures

Component shelves for 800 mm wide network enclosures

Version: Max. load capacity 100 kg

Component shelves, W x D = 671 x 500 mm, 2 mm thick steel sheet version; for installing in 800 mm wide network enclosures.

The component shelf is slotted to prevent the accumulation of heat. The unit base can hold a maximum load of 100 kg.

The height of the fitted component shelves can be adjusted using the 25 mm pitch pattern in network enclosures with a DIN pitch pattern but is infinitely adjustable in network enclosures with aluminium frames.

Material: sheet steel

Paint finish: RAL 7035

Dimensions: W x D: 671 x 500 mm