

**Rittal – The System.**

Faster – better – everywhere.



**TS 8701.060**

**Base/plinth trim panels, side, 100 mm**

State: 23/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8701.060 - Base/plinth trim panels, side, 100 mm Stainless steel for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used. Base/plinth trims may be installed rotated through 90° in order to stabilise bayed base/plinth components.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | TS 8701.060  |
| Product description   | For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trim panels may be used.   |
| Material              | Stainless steel 1.4301 (AISI 304)  |
| Surface finish        | Brushed, grain 400   |
| Supply includes       | 2 base/plinth trim panels<br>Assembly parts  |
| Assembly instruction  | Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose |
| Dimensions            | Height: 100 mm   |
| To fit                | Enclosure type: TS: = 600 mm   |
| Packs of              | 2 pc(s).   |
| Net weight            | 2.572 kg   |
| Gross weight          | 2.8 kg   |
| Customs tariff number | 94039910   |
| ETIM 9                | EC000721   |
| ECLASS 8.0            | 27182003   |
| Product description   | TS Trim panel, sides, H: 100 mm, for W: 600 mm, Stainless steel 1.4301   |