

Rittal – The System.

Faster – better – everywhere.



TS 8802.125

Section for cable entry, rear

State: 23/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8802.125 - Section for cable entry, rear for TS, TP

For mounting directly onto the base opening.

Features

| | |
|-------------------------------------|--|
| Model No. | TS 8802.125 |
| Product description | For sealing the cable entry at the base opening. |
| Benefits | Particularly well-suited to cables with identical cross-sections When installing the mounting plate in the rearmost position, the cables may be routed directly with no large radii. |
| Technical specifications | Foam rubber cable clamp strip: Cross-section: 30 x 25 mm |
| Applications | Mount directly on the base opening/base tray and gland plate |
| Material | Extruded aluminium section Foam rubber cable clamp strip: PU foam |
| Supply includes | Plug-in sections, incl. foam rubber clamp strip |
| Note | 2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm From an enclosure width of 1000 mm, two base openings are provided. 4 packs per enclosure may be fitted |
| To fit | Enclosure type: TS: = 1,200 mm Enclosure type: TP |
| IP protection category to IEC 60529 | IP 55 if installed correctly |
| Packs of | 4 pc(s). |
| Net weight | 0.384 kg |
| Gross weight | 0.433 kg |
| Customs tariff number | 76042990 |
| ETIM 9 | EC002624 |
| ECLASS 8.0 | 27189265 |
| Product description | TS Section for cable entry, rear, for TS, VX SE, TP, for W: 1200 mm |