

Rittal – The System.

Faster – better – everywhere.



SK 7980.100 Fan expansion kit

State: 03/04/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 7980.100 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

Features

| | |
|---|---|
| Model No. | SK 7980.100 |
| Product description | For use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate. |
| Supply includes | Fan Connection cable (0.61 m) Assembly parts |
| Air throughput, unimpeded airflow (with chopped-fibre filter) | At 50 Hz: 108 m ³ /h At 60 Hz: 120 m ³ /h |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 14 W At 60 Hz: 12 W |
| Dimensions | Width: 119 mm Height: 119 mm Depth: 25 mm |
| Operating temperature range | -20 °C...70 °C |
| Noise level | At 50 Hz: 34 dB(A) At 60 Hz: 34 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 0.43 kg |
| Gross weight | 0.486 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | DK Fan expansion kit, for use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate, WxHxD: 119x119x25 mm, 230 V, 1 ~, 50/60 Hz |

Tender text

EL fan expansion kit

Rated operating voltage: 230V;

Power consumption: 14/12

W at 50/60 Hz;

Air throughput (unimpeded air flow): 108/120 m³/h at
50/60 Hz;

Temperature range: -20°C to +70°C

Dimensions (W x H x D): 119 mm x 119 mm x 25 mm