

# Rittal – The System.

Faster – better – everywhere.



## SK 7999.991

## Outdoor climate control with inverter technology

State: 26/07/2025 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 7999.991 - Outdoor climate control with inverter technology for Micro Data Center

Outdoor climate control with inverter technology. The speed control of the compressor and the regulation of refrigerant allow energy savings of up to 40%.

## Features

|                         |  |
|-------------------------|--|
| Model No.               | SK 7999.991  |
| Product description     | The external unit with inverter technology allows targeted speed control of the compressor. The refrigerant volume is regulated via the electronic expansion valve. Adaptation to cooling requirements facilitates energy savings of up to 40%. The cold air is expelled in front of the 482.6 mm (19") level by the internal unit (evaporator coil), while the hot air is drawn in at the rear. Modified air baffle plates achieve additional efficiency gains and help to avoid hot spots. |
| Function principle      | <p>All climate control units for Micro Data Centers are designed as split units to ensure hermetic separation between the cooling circuits inside and outside of the safe. This prevents the ingress of dust and corrosive gases.</p> <p>Air routing inside the safe is horizontal. The hot air is drawn in at the rear, and the cooled air is expelled in front of the 482.6 mm (19") level.</p>  |
| Colour                  | RAL 7035   |
| Supply includes         | Super Digital Inverter external unit<br>Wire remote control<br>DX control kit  |
| Rated current max.      | At 50 Hz: 13.9 A   |
| Start-up current max.   | At 50 Hz: 36 A   |
| Noise Level general min | 48 dB(A)   |
| Noise Level general max | 49 dB(A)   |

# Features

|                             |  |
|-----------------------------|--|
| Dimensions                  | Width: 900 mm<br>Height: 795 mm<br>Depth: 320 mm |
| Operating temperature range | -15 °C...43 °C                                   |
| Pre-fuse                    | Miniature circuit-breaker/fuse: 25 A             |
| Setting range               | -15 °C...43 °C                                   |
| Packs of                    | 1 pc(s).   |
| Customs tariff number       | 84159000   |
| EAN                         | 4028177654129                                    |
| ECLASS 8.0                  | 27180704   |