Rittal – The System.

Faster - better - everywhere.





SV 9340.650 OM adaptors

State: 31/10/2025 (Source: rittal.com/sg-en)



SV 9340.650 - OM adaptors with spring terminals



Features

Model No.	SV 9340.650
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	65 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to- centre spacing	60 mm
Support rail type	Support frame, 1 x TS 55E, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Note on Model No.	According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported
Dimensions	Width: 55 mm Height: 272 mm
Connection of round conductors	2.5 - 16 mm²
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm

© Rittal 2025

Features

Packs of	1 pc(s).
Net weight	0.339
Gross weight	0.377
Copper weight (kg per piece)	0.059
Customs tariff number	85369095
EAN	4028177502673
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM adaptor 65 A

OM adaptor 65 A with tension spring clamp, 3-pole, for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications
Construction width: 55 mm

Length: 208 mm

Support frame: 55 x 237 mm Support frame support: yes

Support rail: 2 with anti-slip guard

System:

Rittal RiLine60

© Rittal 2025