

Rittal – The System.

Faster – better – everywhere.



TS 8612.140

**TS punched section with mounting
flange, 17 x 73 mm**

State: 28/06/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.140 - TS punched section with mounting flange, 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

| | |
|----------------------|--|
| Model No. | TS 8612.140 |
| Design | For the outer mounting level |
| Product description | For universal skeleton structures or partial assembly. Simply locate into the punchings and secure. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly screws |
| Length | 340 mm |
| Installation options | On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round On the horizontal VX SE enclosure section, top in the depth In TP via rail for interior installation: In the width, for inner mounting level As a mounting kit for component shelves in TS, VX SE, simply locate and secure |
| Assembly instruction | The rail for internal mounting is required when installing in TP |

Features

| | |
|-------------------------------|--|
| To fit | Enclosure type: VX SE TP PC IW Width/depth: 400 mm |
| Packs of | 4 pc(s). |
| Net weight | 1.4 kg |
| Gross weight | 1.46 kg |
| PCF per pack (cradle-to-gate) | 6.1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | TS punched section with mounting flange, 17 x 73 mm, for outer mounting level: W/D: 400 mm, L: 340 mm |