Rittal – The System.

Faster – better – everywhere.



SV 9343.230

NH fuse-switch disconnector

State: 02/11/2026 (Source: www.rittal.com/sg-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9343.230 - NH fuse-switch disconnector with electronic fuse monitoring

Features

Model No.	SV 9343.230
Design	with electronic fuse monitoring For 60 mm busbar systems with electronic fuse monitoring
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 50 mm Clamping area height: 10 mm
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	400 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	2
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection of round conductors	10 - 240 mm²
To fit busbars	Height: 5, 10 mm
Number of poles	3-pole

© Rittal 2026

Features

with electronic fuse monitoring	Yes
Round conductor cross-section	10 - 240 mm²
Packs of	1 pc(s).
Net weight	3.2 kg
Gross weight	3.52 kg
Copper weight (kg per piece)	1
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnector, size 2, 400 A, 400-690 V, 3-pole, screw M10, with electronic fuse monitoring

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK