

Rittal – The System.

Faster – better – everywhere.



SV 9341.050 Busbar support PLS

State: 15/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9341.050 - Busbar support PLS

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.

Features

Model No.	SV 9341.050
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated operating voltage	1000 V, 3~ 1500 V (DC)
Electrical ratings UL (SCCR)	14 kA - 600 V, support spacing 500 mm, PLS 800 busbars 22 kA - 600 V, support spacing 200 mm, PLS 800 busbars 50 kA - 600 V, support spacing 250 mm, PLS 800 busbars, circuit breaker max. 600 A, DIVQ/7 50 kA - 600 V, support spacing 250 mm, PLS 800 busbars, Fuse Class L max. 800 A, JDDZ/7 65 kA - 480 V, support spacing 150 mm, PLS 800 busbars, circuit breaker max. 600 A, DIVQ/7 65 kA - 600 V, support spacing 150 mm, PLS 800 busbars, Fuse Class max. 600 A, JDDZ/7
Note on Model No.	The use of a base tray is required for UL applications UL approval only applies in conjunction with AC application
Top-mounting	Yes
Number of poles	3-pole
To fit busbars	PLS 800
To fit Model No.	3516.000 3527.000 3528.000 3528.010 3529.000
Internal attachment	Yes

Features

Centre-to-centre spacing of busbars	60 mm
Approvals	UL
Packs of	4 pc(s).
Net weight	0.32 kg
Gross weight	0.368 kg
Customs tariff number	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV Busbar support, PLS 800, 3-pole, 60 mm bar centre distance, UL design

Approvals

Approvals	ABS Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

PLS 800 UL busbar support

PLS 800 UL busbar support

3-pole

Technical specifications

Bar centre distance: 60 mm

Busbars: PLS 800 special busbar

Construction width: 20 mm

Length: 190 mm

Note

The use of the base tray is compulsory for UL applications.