Rittal - The System.

Faster - better - everywhere.





SV 9635.400 Motor controller

State: 11/11/2025 (Source: rittal.com/sg-en)



SV 9635.400 - Motor controller 3-pole

For controlling motors as direct or reversing starters with integral over-ride protection

Features

Model No.	SV 9635.400	
Function principle	For controlling motors as direct or reversing starters with integral over-ride protection The hybrid technology used facilitates frequent switching by semi-conductors with zero wear During operation, mechanical contacts ensure a low heat loss Space-saving configuration thanks to the minimal build width	
Material	Polyamide Fire protection corresponding to UL 94-V0	
Colour	RAL 7035	
Power dissipation (max.)	2.8 W	
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz	
Rated current max.	0.6 A	
Note	The technical data may vary for UL applications	
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm	
Connection of round conductors	0.14 - 2.5 mm²	
Adjustable current monitoring	0.075 - 0.6 A	
Packs of	1 pc(s).	
Net weight	0.38	
Gross weight	0.389	
Customs tariff number	85371091	
EAN	4028177817319	
ETIM 9	EC002572	

© Rittal 2025

Features

8 8.0 27370804

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3