

# Rittal – The System.

Faster – better – everywhere.



## SV 9676.704 Connection plate

State: 07/12/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9676.704 - Connection plate for ring terminals

For connecting ring terminals to a Flat-PLS busbar system with 2 – 4 bars per conductor.

## Features

|                              |                                                                                                                                                                                                       |
|------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                    | SV 9676.704                                                                                                                                                                                           |
| Product description          | For connecting ring terminals to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness.                                                                                 |
| Material                     | Connection plate: E-Cu, nickel-plated<br>Busbar claw: Stainless steel                                                                                                                                 |
| Supply includes              | Assembly parts (excluding screws)                                                                                                                                                                     |
| Assembly instruction         | The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply.<br>Busbar claw with threaded insert M10 |
| Dimensions                   | Thread: M16                                                                                                                                                                                           |
| Packs of                     | 1 pc(s).                                                                                                                                                                                              |
| Net weight                   | 0.659                                                                                                                                                                                                 |
| Gross weight                 | 0.66                                                                                                                                                                                                  |
| Copper weight (kg per piece) | 0.49                                                                                                                                                                                                  |
| Customs tariff number        | 73269098                                                                                                                                                                                              |
| EAN                          | 4028177625761                                                                                                                                                                                         |
| ETIM 9                       | EC001900                                                                                                                                                                                              |
| ECLASS 8.0                   | 27400613                                                                                                                                                                                              |