Rittal – The System.

Faster – better – everywhere.



SV 9343.200

NH fuse-switch disconnector

State: 02/11/2026 (Source: www.rittal.com/sg-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9343.200 - NH fuse-switch disconnector

Features

Model No.	SV 9343.200
Design	For 60 mm busbar systems
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 32 mm Clamping area height: 10 mm
Note	Connection of sector-shaped conductors 120 – 300 mm².
For bar systems with centre-to-centre spacing	60 mm
Note	The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses".
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Rated operating current max.	400 A
Rated operating voltage	690 V, 3~
For NH size	2
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection of round conductors	95 - 300 mm²
To fit busbars	Height: 5, 10 mm

© Rittal 2026

Features

Clamping area for laminated copper bars	20 mm
Number of poles	3-pole
Round conductor cross-section	95 - 300 mm²
Packs of	1 pc(s).
Net weight	3.42 kg
Gross weight	3.62 kg
Copper weight (kg per piece)	1
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnector, size 2, 400 A, 690 V, 3-pole, box terminal

Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK