

# Rittal – The System.

Faster – better – everywhere.



## AX 1015.000

## Osnovno ohišje AX, nerjavno jeklo

State: 9.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 1015.000 - Osnovno ohišje AX, nerjavno jeklo

Ohišja so izdelana iz robustnega nerjavnega jekla in imajo integriran odmični sistem, ki omogoča obsežno razširitev sistema, hitro in varno, brez vrtanja.



## Features

Št. Modela	AX 1015.000
Material	Ohišje: nerjavno jeklo Vrata: nerjavno jeklo, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina Nerjavno jeklo 1.4301 (AISI 304)
Površinska obdelava	Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm Montažna plošča: pocinkana
Obseg dobave	Ohišje z vrati, kot odpiranja 130° Montažna plošča Ključavnica: 3 mm dvojna ključavnica
Razred zaščite NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Razred zaščite po IEC 60 529	IP 66
Tipna ocena po UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12

## Features

IK koda	IK10
Mere	Širina: 400 mm Višina: 500 mm Globina: 210 mm
Debelina materiala - vrata	1,5 mm
Debelina materiala - ohišje	1,25 mm
Debelina materiala montažne plošče	2 mm
Mere montažne plošče (Š x V)	350 mm x 475 mm
Število vrat	1
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 2 Vložek ključavnice: 3 mm dvojni nastavek Material lock: Tlačno liti cink
Osnovni material	Stainless steel 1.4301 (AISI 304)
Paketi	1 pc(s).
Neto teža	11,2 kg
Bruto teža	11,95 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	AX Compact enclosure, WHD: 400x500x210 mm, stainless steel 1.4301, with mounting plate, single-door, with two cam locks

## Approvals

# Approvals

---

Approvals

Bureau Veritas  
DNV-GL  
Lloyds Register of Shipping  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
PCF-declaration