Rittal – The System.

Faster – better – everywhere.



SV 9344.230

NH fuse-switch disconnector

State: 02/11/2026 (Source: www.rittal.com/sg-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9344.230 - NH fuse-switch disconnector with electronic fuse monitoring

Features

Model No.	SV 9344.230
Design	with electronic fuse monitoring For mounting plate assembly
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 50 mm Clamping area height: 10 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	400 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	2
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection of round conductors	10 - 240 mm²
Number of poles	3-pole
with electronic fuse monitoring	Yes
Round conductor cross-section	10 - 240 mm²

© Rittal 2026

Features

Packs of	1 pc(s).
Net weight	3.178 kg
Gross weight	3.18 kg
Copper weight (kg per piece)	1
Customs tariff number	85365080
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnector, size 2, 400 A, 400-690 V, 3-pole, screw M10, with electronic fuse monitoring, for mounting plate assembly

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK